

## Backflow Special Check Valve Devices

### BACKFLOW DIRECT L L C

EX26602

2484 Merchantile Dr

Rancho Cordova, CA 95742 USA

Backflow Special check valves for a maximum working pressure of 175 psi in the following models, types and sizes.

Model	Type	Size In.	Installation Orientation
<i>Deringer 20</i>	DC	2-1/2, 3, 4, 8	H, V
<i>Deringer 20G</i>	DC	2-1/2, 3, 4, 8	H, V
<i>Deringer 20X</i>	DC	6	H, V
<i>Deringer 20GX</i>	DC	6	H, V
<i>Deringer 30</i>	DCDA	2-1/2, 3, 4, 8	H, V
<i>Deringer 30G</i>	DCDA	2-1/2, 3, 4, 8	H, V
<i>Deringer 30X</i>	DCDA	6	H, V
<i>Deringer 30GX</i>	DCDA	6	H, V
<i>Deringer 40</i>	RP	2-1/2, 3, 4, 8	H
<i>Deringer 40G</i>	RP	2-1/2, 3, 4, 8	H
<i>Deringer 40X</i>	RP	6	H
<i>Deringer 40GX</i>	RP	6	H
<i>Deringer 50</i>	RPDA	2-1/2, 3, 4, 8	H
<i>Deringer 50G</i>	RPDA	2-1/2, 3, 4, 8	H
<i>Deringer 50X</i>	RPDA	6	H
<i>Deringer 50GX</i>	RPDA	6	H

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2019 UL LLC"